



# Locking Devices, Bryant Power Interrupting, Industrial, Male Plug, 20A 125V/10A 250V DC 480V AC, Non-NEMA

By Bryant  
Catalog # 23005G

Locking Devices, Bryant Power Interrupting, Industrial, Male Plug, 20A 125V AC or DC, 10A 250V DC 480V AC, 2-Pole 3-Wire Grounding, Non-NEMA, Screw Terminal, Black/White



## Features

- Molded-in male contacts are resistant to damage and provide a consistently positive connection
- Insulated non-metallic housing enhances safety and abuse resistance
- Box terminals in conjunction with screws with pressure pads provide maximum termination strength and dependability
- Three-piece clamp assembly provides maximum strain relief and protects against entry of moisture and dust

## Application

Extra Heavy Duty Industrial

## General

Color	Black, White
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	10A/20A Male Nylon Plug
Material	Composite
Material - Mounting Hardware	Cord Mounted
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Style	Grounding
Type	Plugs
UPC	781786618886

## Dimensions

Dimensions	1.72 in x 1.72 in x 3.22 in
Display Size	Standard Sized
Height	3.22 in
Length	1.72 in
Width	1.72 in

## Electrical Ratings

Amperage Rating	20A/10 A
Connectivity	Screw Terminals
Current Rating	20A/10 A
Phase	Single Phase
Voltage Rating	125 VAC/125 VDC/250 VDC/480 VDC
Voltage Rating Description	125 VAC/125 VDC/250 VDC/480 VDC

## Conductor Related

Cord Type	All Listed Portables
Number Of Wires	3-Wire
Wire Size	#14 AWG to #10 AWG

## Logistics

Carton Quantity	20
-----------------	----

## Product Assets

[Catalog Page - Bryant H-24 Catalog page](#)  
[Catalogs - Bryant Full Line Catalog](#)

## Related Products

[20425 - Locking Devices, Bryant Power Interrupting, Accessories, Weatherproof Boot for Plug, For 30A Black Rubber](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRY-23005G-SPEC-EN | REV 5/2023