



Locking Devices, Bryant Power Interrupting, Industrial, Receptacle, 30A 250V DC/600V AC, Non-NEMA, Screw Terminal, FS/FD Mounting

By Bryant
Catalog # 25250



Locking Devices, Bryant Power Interrupting, Industrial, Receptacle, 30A 600V AC/ 20A 250V DC, 4-Pole 5-Wire Grounding, Non-NEMA, Screw Terminal, Black, Aluminum weather protective housing/cover for F.S. and F.D. boxes

Features

- Spring loaded safety shutter contains arcing when mating or un-mating devices under load
- Spring loaded safety shutter automatically ejects the plug eliminating contact teasing
- Box terminals in conjunction with screws with pressure pads provide maximum termination strength and dependability
- Metallic weather protective spring loaded cover provides protection from moisture and dust

General

Application	Industrial Grade
Catalog Number	25250
EU RoHS Indicator	No
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	20A/30A Flush Single Receptacle
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	4-Pole
OEM Brand Name	Hubbell Bryant
Style	Grounding
Type	Receptacle
UPC	781786683402

Dimensions

Dimensions	4.56 in x 2.84 in x 1.69 in
Display Size	Standard Sized Product
Height	1.69 in
Length	4.56 in
Width	2.84 in

Electrical Ratings

Amperage Rating	20A/30 A
Connectivity	Terminal Screws
Current Rating	20A/30 A
Phase	Multi Phase
Voltage Rating	250 VDC/600 VAC
Voltage Rating Description	250 VDC/600 VAC

Conductor Related

Number Of Wires	5-Wire
Wire Size	#14 AWG to #10 AWG

Logistics

Carton Quantity	8
-----------------	---

Product Assets

[Catalog Page - BRY H-25 Catalog Page](#)
[Catalogs - Bryant Full Line Catalog](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRY-25250-SPEC-EN | REV 6/2024