



# Locking Devices, Bryant Power Interrupting, Industrial, Male Plug, 60A 250V DC/600V AC, 4-Pole 5-Wire Grounding, Non-NEMA, Screw Terminal and White

By Bryant  
Catalog # 25415



Locking Devices, Bryant Power Interrupting, Industrial, Male Plug, 20A 250V DC/30A 600V AC, 4-Pole 5-Wire Grounding, Non-NEMA, Screw Terminal, Black nylon with cord grip

## Features

- Molded-in male contacts are resistant to damage and provide a consistently positive connection
- Insulated non-metallic housing enhances safety and abuse resistance
- Box terminals in conjunction with screws with pressure pads provide maximum termination strength and dependability
- Three-piece clamp assembly provides maximum strain relief and protects against entry of moisture and dust

## General

Application	Extra Heavy Duty Industrial
Catalog Number	25415
Color	Black
EU RoHS Indicator	No
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	20A/30A Male Plug
Material	Composite
Material - Mounting Hardware	Cord Mounted
Number Of Poles	4-Pole
OEM Brand Name	Hubbell Bryant
Style	Grounding
Type	Plugs
UPC	781786684003

## Dimensions

Dimensions	2.50 in x 2.50 in x 6.56 in
Display Size	Standard Sized
Height	6.56 in
Length	2.5 in
Width	2.5 in

## Electrical Ratings

Amperage Rating	20A/30 A
Connectivity	Screw Terminals
Current Rating	20A/30 A
Phase	Multi Phase
Voltage Rating	250 VDC/600 VAC
Voltage Rating Description	250 VDC/600 VAC
Wattage	

## Conductor Related

Cord Type	All Listed Portables
Number Of Wires	5-Wire
Wire Size	#14 AWG to #10 AWG

## Logistics

Carton Quantity	5
-----------------	---

## Product Assets

[Catalog Page - BRY H-25 Catalog Page](#)  
[Catalogs - Bryant Full Line Catalog](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
BRY-25415-SPEC-EN | REV 6/2024