



Locking Devices, Bryant Power Interrupting, Industrial, Male Plug, 60A 600V AC, 4-Pole 5-Wire Grounding, Non-NEMA, Screw Terminal, Blue

By Bryant
Catalog # 26519



Locking Devices, Bryant Power Interrupting, Industrial, Male Plug, 60A 600V AC, 4-Pole 5-Wire Grounding, Non-NEMA, Screw Terminal, Blue polycarbonate outer cover and adjustable cord grip

Features

- Molded-in male contacts are resistant to damage and provide a consistently positive connection
- Insulated, color coded metallic housing enhances safety and abuse resistance
- Box terminals in conjunction with stainless steel terminal screws provide maximum termination strength and dependability

General

Application	Extra Heavy Duty Industrial
Catalog Number	26519
Color	Blue
EU RoHS Indicator	No
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	60A Male Plug
Material	Composite
Material - Mounting Hardware	Cord Mounted
Number Of Poles	4-Pole
OEM Brand Name	Hubbell Bryant
Style	Grounding
Type	Plugs
UPC	781786574199

Dimensions

Dimensions	3.03 in x 4.65 in x 4.65 in
Display Size	Standard Sized
Height	4.65 in
Length	3.03 in
Width	4.65 in

Electrical Ratings

Amperage Rating	60 A
Connectivity	Screw Terminals
Current Rating	60 A
Phase	Multi Phase
Voltage Rating	600 VAC
Voltage Rating Description	600 VAC
Wattage	

Conductor Related

Cord Type	All Listed Portables
Number Of Wires	5-Wire
Wire Size	#14 AWG to #10 AWG

Logistics

Carton Quantity	5
-----------------	---

Product Assets

[Catalog Page - BRY H-26 Catalog Page](#)
[Catalogs - Bryant Full Line Catalog](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRY-26519-SPEC-EN | REV 6/2024