



Locking Devices, Bryant Power Interrupting, Industrial, Flanged Receptacle, 60A 600V AC, 4-Pole 5-Wire Grounding, Non-NEMA, Screw Terminal, Blue

By Bryant
Catalog # 26521



Locking Devices, Bryant Power Interrupting, Industrial, Flanged Receptacle, 60A 600V AC, 4-Pole 5-Wire Grounding, Non-NEMA, Screw Terminal, Steel housing

Features

- Spring loaded safety shutter contains arcing when mating or un-mating devices under load
- Spring loaded safety shutter automatically ejects the plug eliminating contact teasing
- Box terminals in conjunction with stainless steel terminal screws provide maximum termination strength and dependability
- Metallic housing provides protection from damage in harsh environments

Application

Extra Heavy Duty Industrial Specification Grade

General

Color	Blue
Environmental Conditions	Indoor Only
Item Type	60A Flanged Single Receptacle
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	4-Pole
OEM Brand Name	Hubbell Bryant
Style	Grounding
Type	Flanged Receptacle
UPC	781786574212

Dimensions

Dimensions	4.12 in x 4.12 in x 4.53 in
Display Size	Standard Sized Product
Height	4.53 in
Length	4.12 in
Width	4.12 in

Electrical Ratings

Amperage Rating	60 A
Connectivity	Pressure Terminal Screws
Current Rating	60 A
Phase	Multi Phase
Voltage Rating	600 VAC
Voltage Rating Description	600V AC

Conductor Related

Number Of Wires	5-Wire
Wire Size	#18 AWG to #8 AWG

Logistics

Carton Quantity	5
-----------------	---

Product Assets

[Catalog Page - Bryant H-26 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)

Related Products

26519 - Locking Devices, Bryant Power Interrupting, Industrial, Male Plug, 60A 600V AC, 4-Pole 5-Wire Grounding, Non-NEMA, Screw Terminal, Blue



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-26521-SPEC-EN | REV 5/2023