



# Straight Blade Devices, Specialty Receptacles, Clock Hanger, Receptacle and Plate, 15A 125V, 5-15R, Smooth Brushed Brass Plate

By Bryant  
Catalog # 2828G



Straight Blade Devices, Specialty Receptacles, Clock Hanger, Receptacle and Plate, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, Smooth Brushed Brass Plate, Single Pack

### General

Application	Commercial/Industrial
Catalog Number	2828G
Color	Brass
EU RoHS Indicator	No
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Clock Hanger Single
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Series	Special Use
Style	Clock Hanger / Recessed Receptacles
Type	Single Receptacle
UPC	781786619012

### Dimensions

Dimensions	4.63 in x 2.88 in x 2.10 in
Display Size	Standard Sized Product
Height	2.1 in
Length	4.63 in
Weight	0.45 lb
Width	2.88 in

### Electrical Ratings

Amperage Rating	15 A
Current / Amperage Rating	15 A
Current Rating	15 A
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V
Wattage	1875

### Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #12 AWG

### Certifications And Compliance

Nema Rating	5-15R
-------------	-------

### Logistics

Carton Quantity	10
-----------------	----

### Product Assets

[Catalog Page - BRY A-24 Catalog Page](#)  
[Catalogs - Bryant Full Line Catalog](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
BRY-2828G-SPEC-EN | REV 6/2024