



## Switches and Lighting Controls, Industrial Grade, Toggle Switches, Motor Disconnects, Three Pole, 30A 600V AC, Back and Side Wired, Short Toggle

By Bryant  
Catalog # 30003DS



Switches and Lighting Controls, Industrial Grade, Toggle  
Switches, Motor Disconnects, Three Pole, 30A 600V AC, Back  
and Side Wired, Black, Short Toggle

### General

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Open Switch
Load Capacity	Inductive
Material - Mounting Hardware	Screw Mounting
Number Of Poles	3 Pole
OEM Brand Name	Hubbell Bryant
Operating Cycles	10,000 Cycles Minimum
Operating Temperature	Minimum Continuous -40 Deg C without Impact
Series	Short Toggle
Style	Motor Controller/Disconnect
Type	Back & Side Wire
UPC	781786631540

### Dimensions

Display Size	Standard Sized Product
--------------	------------------------

### Electrical Ratings

Amperage Rating	30 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	30 A
Current Rating	30 A
Phase	Three Phase
Voltage Rating	600V AC kV
Voltage Rating Description	600V AC kV
Wattage	18000

### Logistics

Carton Quantity	10
-----------------	----

### Product Assets

[Catalog Page - Bryant E-12 Catalog page](#)  
[Catalog Page - Bryant G-6 Catalog page](#)  
[Catalog Page - Bryant G-2 Catalog page](#)  
[Catalogs - Bryant Full Line Catalog](#)  
[Literature - General Literature - Motor Controllers and  
Disconnects](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRY-30003DS-SPEC-EN | REV 5/2023