



# Extra Heavy Duty Industrial Grade, Toggle Switches, General Purpose AC, Single Pole, 30A 120/277V AC, Back and SideWired, Brown

By Bryant  
Catalog # 3001

Switches and Lighting Controls, Extra Heavy Duty Industrial Grade, Toggle Switches, General Purpose AC, Single Pole, 30A 120/277V AC, Back and SideWired, Brown



## Application

Back and Side Wired

## General

Color	Brown
Series	Extra Heavy Duty
Style	Single Pole
Type	Toggle
UPC	781786619203

## Electrical Ratings

Amperage Rating	30 A
Current / Amperage Rating	30 A
Voltage Rating	120/277 VAC
Voltage Rating Description	120/277 VAC

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

[Catalog Page - Bryant E-2 Catalog page](#)  
[Catalogs - Bryant Full Line Catalog](#)

## Related Products

- [3002BRN - Extra Heavy Duty Industrial Grade, Toggle Switches, General Purpose AC, Double Pole, 30A 120/277V AC, Back and Side Wired, Brown](#)
- [3001I - Extra Heavy Duty Industrial Grade, Toggle Switches, General Purpose AC, Single Pole, 30A 120/277V AC, Back and Side Wired](#)
- [3025BRN - Industrial Grade, Toggle Switches, General Purpose AC, Double-Pole Double-Throw Center Off, 30A120/277V AC, Back and Side Wired, Brown](#)
- [SS1 - Wallplates and Boxes, Metallic Plates, 1- Gang, 1\) Toggle Opening, Standard Size, Stainless Steel](#)
- [3001PLR120 - Pilot Light, Extra Heavy Duty Industrial Grade, Toggle Switches, General Purpose AC, Single Pole, 30A 120V AC, Back and Side Wired](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRY-3001-SPEC-EN | REV 5/2023