



Industrial Grade, Toggle Switches, General Purpose AC, Double-Pole Double-Throw Center Off, 30A120/277V AC, Back and Side Wired, Brown

By Bryant
Catalog # [3025BRN](#)

Switches and Lighting Controls, Industrial Grade, Toggle
Switches, General Purpose AC, Double-Pole Double-Throw
Center Off, 30A120/277V AC, Back and Side Wired, Brown



Application

Back and Side Wired

General

| | |
|--------|--------------------------|
| Color | Brown |
| Series | Extra Heavy Duty |
| Style | Double Pole Double Throw |
| Type | Toggle |
| UPC | 781786650305 |

Electrical Ratings

| | |
|----------------------------|-------------|
| Amperage Rating | 30 A |
| Current / Amperage Rating | 30 A |
| Voltage Rating | 120/277 VAC |
| Voltage Rating Description | 120/277 VAC |

Logistics

| | |
|-----------------|----|
| Carton Quantity | 10 |
|-----------------|----|

Product Assets

[Catalog Page - Bryant E-3 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)

Related Products

- [3002GRY - Extra Heavy Duty Industrial Grade, Toggle Switches, General Purpose AC, Double Pole, 30A 120/277V AC, Back and Side Wired](#)
- [3002PLR120 - Pilot Light, Extra Heavy Duty Industrial Grade, Toggle Switches, General Purpose AC, Double Pole, 30A 120V AC, Back and Side Wired](#)
- [3002PLR277 - Pilot Light, Extra Heavy Duty Industrial Grade, Toggle Switches, General Purpose AC, Double Pole, 30A 277V AC, Back and Side Wired](#)
- [3003BRN - Extra Heavy Duty Industrial Grade, Toggle Switches, General Purpose AC, Three Way, 30A 120/277V AC, Back and Side Wired, Brown](#)
- [P1 - Wallplate, Toggle, 1-Gang, Brown](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-3025BRN-SPEC-EN | REV 5/2023