



Industrial Grade, Toggle Switches, General Purpose AC, Double-Pole Double-Throw Center Off, 30A120/277V AC, Back and Side Wired

By Bryant
Catalog # 3025I

Switches and Lighting Controls, Industrial Grade, Toggle
Switches, General Purpose AC, Double-Pole Double-Throw
Center Off, 30A120/277V AC, Back and Side Wired, Ivory



Application

Back and Side Wired

General

Color	Brown
Series	Extra Heavy Duty
Style	Double Pole Double Throw
Type	Toggle
UPC	781786650336

Electrical Ratings

Amperage Rating	30 A
Current / Amperage Rating	30 A
Voltage Rating	120/277 VAC
Voltage Rating Description	120/277 VAC

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - Bryant E-3 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)

Related Products

[3003BRN - Extra Heavy Duty Industrial Grade, Toggle
Switches, General Purpose AC, Three Way, 30A 120/277V AC,
Back and Side Wired, Brown](#)
[3001 - Extra Heavy Duty Industrial Grade, Toggle Switches,
General Purpose AC, Single Pole, 30A 120/277V AC, Back and
SideWired, Brown](#)
[3003GRY - Extra Heavy Duty Industrial Grade, Toggle
Switches, General Purpose AC, Three Way, 30A 120/277V AC,
Back and Side Wired](#)
[PII - Wallplate, Toggle, 1-Gang, Ivory](#)
[3025BRN - Industrial Grade, Toggle Switches, General Purpose
AC, Double-Pole Double-Throw Center Off, 30A120/277V AC,
Back and Side Wired, Brown](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-3025I-SPEC-EN | REV 5/2023