



Switches and Lighting Controls, Industrial Grade, Toggle Switches, Motor Disconnects, Three Pole, 30A 600V AC, Side Wired Only, With NEMA 3R Enclosure

By Bryant
Catalog # 30303D



Switches and Lighting Controls, Industrial Grade, Toggle
Switches, Motor Disconnects, Three Pole, 30A 600V AC, Side
Wired Only, Black, With NEMA 3R Enclosure

Application

Red Slide

General

Enclosure Type	NEMA 3R
Environmental Conditions	Indoor and Outdoor
Item Type	Enclosed Switch
Load Capacity	Inductive
Material - Mounting Hardware	Screw Mounting
Number Of Poles	3 Pole
OEM Brand Name	Hubbell Bryant
Operating Cycles	10,000 Cycles Minimum
Operating Temperature	Minimum Continuous -40 Deg C without Impact
Series	Non-Fused
Style	Standard Duty
Type	Disconnect Switches
UPC	781786631588

Dimensions

Display Size	Standard Sized Product
--------------	------------------------

Electrical Ratings

Amperage Rating	30 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	30 A
Current Rating	30 A
Phase	Three Phase
Voltage Rating	600V AC kV
Voltage Rating Description	600V AC kV
Wattage	18000

Logistics

Carton Quantity	4
-----------------	---

Product Assets

[Catalog Page - Bryant E-12 Catalog page](#)
[Catalog Page - Bryant G-6 Catalog page](#)
[Catalog Page - Bryant G-3 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Literature - General Literature - Motor Controllers and Disconnects](#)
[Literature - General Literature - BRYANT® Wiring Devices](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-30303D-SPEC-EN | REV 4/2023