




Switches and Lighting Controls, Industrial Grade, Toggle Switches, Motor Disconnects, Three Pole, 30A 600V AC, Side Wired Only, NEMA 3R Box and Switch

By Bryant
Catalog # 30323D



Switches and Lighting Controls, Industrial Grade, Toggle Switches, Motor Disconnects, Three Pole, 30A 600V AC, Side Wired Only, Black, NEMA 3R Box and Switch

Application

Red Handle

General

Enclosure Type	NEMA 3/3R
Environmental Conditions	Indoor and Outdoor
Item Type	Enclosed Switch
Load Capacity	Inductive
Material - Mounting Hardware	Screw Mounting
Number Of Poles	3 Pole
OEM Brand Name	Hubbell Bryant
Operating Cycles	10,000 Cycles Minimum
Operating Temperature	Minimum Continuous -40 Deg C without Impact
Series	Non-Fused
Style	Standard Duty
Type	Disconnect Switches
UPC	781786631625

Dimensions

Display Size	Standard Sized Product
--------------	------------------------

Electrical Ratings

Amperage Rating	30 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	30 A
Current Rating	30 A
Phase	Three Phase
Voltage Rating	600V AC kV
Voltage Rating Description	600V AC kV
Wattage	18000

Logistics

Carton Quantity	4
-----------------	---

Product Assets

[Catalog Page - Bryant E-12 Catalog page](#)
[Catalog Page - Bryant G-6 Catalog page](#)
[Catalog Page - Bryant G-3 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)
[Literature - General Literature - Motor Controllers and Disconnects](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-30323D-SPEC-EN | REV 4/2023