



# Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Male Flanged Inlet, 100A 250V AC, Watertight

By Bryant  
Catalog # 3100B6W



Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Male Flanged Inlet, 100A 250V AC, 2-Pole 3-Wire Grounding, Terminal Screw, Blue, Watertight

## Features

- Industrial Grade
- Male Flanged Inlet
- 100A 250V AC
- 2-Pole 3-Wire Grounding
- Terminal Screw

## Application

High Ampacity Watertight Connections

## General

Catalog Number	3100B6W
Color	Blue
EU RoHS Indicator	Yes
Environmental Conditions	Watertight
Insulation	Insulated Body
Item Type	Single Flanged
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Series	Watertight - IP67
Temperature Rating	Maximum Continuous: 75° C; Minimum Continuous: -40° C

Type	w/o impact
UPC	Inlet 781786250109

## Dimensions

Display Size	Standard Sized Product
--------------	------------------------

## Electrical Ratings

Amperage Rating	100 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	100 A
Current Rating	100 A
Dielectric Strength	Withstands 3000V Minimum in
Voltage Rating	250 VAC
Voltage Rating Description	250V AC
Wattage	25000

## Conductor Related

Number Of Wires	3-Wire
-----------------	--------

## Product Assets

[Specifications - 3100B6W](#)