



Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Male Plug, 16A 200-240V, 2-Pole 3-Wire Grounding, Terminal Screw, Splash Proof

By Bryant
Catalog # 316P6S



Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Male Plug, 16A 200-240V, 2-Pole 3-Wire Grounding, Terminal Screw, Blue, Splash Proof

Application

High Ampacity Connections

General

Color	Blue
Environmental Conditions	Splash Proof
Item Type	Male Plug
Material	Composite
Material - Mounting Hardware	Cord Mounted
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Series	Splashproof - IP44
Type	Plugs
UPC	781786252165

Dimensions

Display Size	Standard Sized
--------------	----------------

Electrical Ratings

Amperage Rating	16 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	16 A
Current Rating	16 A
Phase	Single Phase
Voltage Rating	200-250 V
Voltage Rating Description	200-250 V
Wattage	4000

Conductor Related

Cord Type	All Portable
Number Of Wires	3-Wire
Wire Size	#14 AWG to #10 AWG

Certifications and Compliance

Nema Rating	Non-NEMA
-------------	----------

Product Assets

[Catalog Page - Bryant K-7 Catalog page](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-316P6S-SPEC-EN | REV 5/2023