



Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Female Receptacle, 16A 100-130V, Watertight

By Bryant
Catalog # [316R4W](#)



Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Female Receptacle, 16A 100-130V, 2-Pole 3-Wire Grounding, Terminal Screw, Yellow, Watertight

Features

- Industrial Grade
- Female Receptacle
- 16A 100-130V
- 2-Pole 3-Wire Grounding
- Terminal Screw

Application

High Ampacity Connections

General

Catalog Number	316R4W
Color	Yellow
EU RoHS Indicator	Yes
Environmental Conditions	Watertight
Item Type	Single Flanged
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Series	Watertight - IP67
Type	Receptacle
UPC	781786250246

Dimensions

Display Size Standard Sized Product

Electrical Ratings

Amperage Rating	16 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	16 A
Current Rating	16 A
Phase	Single Phase
Voltage Rating	100-130 V
Voltage Rating Description	100-130V
Wattage	2080

Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #10 AWG

Certifications And Compliance

Nema Rating	Non-NEMA
-------------	----------

Product Assets

[Specifications - 316R4W](#)