



# Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Male Flanged Inlet, 20A 480V AC, Watertight

By Bryant  
Catalog # [320B7W](#)



Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Male Flanged Inlet, 20A 480V AC, 2-Pole 3-Wire Grounding, Terminal Screw, Red, Watertight

## Application

High Ampacity Watertight Connections

## General

Color	Red
Environmental Conditions	Watertight
Insulation	Insulated Body
Item Type	Single Flanged
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Series	Watertight - IP67
Temperature Rating	Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact
Type	Inlet
UPC	781786250284

## Dimensions

Display Size Standard Sized Product

## Electrical Ratings

Amperage Rating	20 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	20 A
Current Rating	20 A
Dielectric Strength	Withstands 3000V Minimum in
Voltage Rating	480 VAC
Voltage Rating Description	480V AC
Wattage	5540

## Conductor Related

Number Of Wires 3-Wire

## Product Assets

[Catalog Page - Bryant K-4 Catalog page](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRY-320B7W-SPEC-EN | REV 5/2023