



Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Female Connector Body, 20A 125V AC, Watertight

By Bryant
Catalog # [320C4W](#)

Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Female Connector Body, 20A 125V AC, 2-Pole 3-Wire Grounding, Terminal Screw, Yellow, Watertight

Features

- Industrial Grade
- Female Connector Body
- 20A 125V AC
- 2-Pole 3-Wire Grounding
- Terminal Screw

Application

High Ampacity Connections

General

| | |
|------------------------------|---|
| Catalog Number | 320C4W |
| Color | Yellow |
| EU RoHS Indicator | Yes |
| Environmental Conditions | Watertight |
| Insulation | Insulated Body |
| Item Type | Watertight |
| Material | Composite |
| Material - Mounting Hardware | Cord Mounted |
| Number Of Poles | 2-Pole |
| OEM Brand Name | Hubbell Bryant |
| Series | Watertight - IP67 |
| Temperature Rating | Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact, -25° with impact. |



| | |
|------|--------------|
| Type | Connector |
| UPC | 781786250291 |

Dimensions

| | |
|--------------|------------------------|
| Display Size | Standard Sized Product |
|--------------|------------------------|

Electrical Ratings

| | |
|----------------------------|--------------------------|
| Amperage Rating | 20 A |
| Connectivity | Pressure Terminal Screws |
| Current / Amperage Rating | 20 A |
| Current Rating | 20 A |
| Voltage Rating | 125 VAC |
| Voltage Rating Description | 125V AC |

Conductor Related

| | |
|----------------------|--------------------|
| Conductor Range | #14 AWG to #10 AWG |
| Number Of Wires | 3-Wire |
| Number of Conductors | 3-Wire Grounding |

Certifications And Compliance

| | |
|-------------|----------|
| Nema Rating | Non-NEMA |
|-------------|----------|

Product Assets

[Specifications - 320C4W](#)



A Hubbell brand