

Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Female Connector Body, 20A 480V AC, Watertight

By Bryant
Catalog # 320C7W



Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Female Connector Body, 20A 480V AC, 2-Pole 3-Wire Grounding, Terminal Screw, Red, Watertight

Features

- Industrial Grade
- Female Connector Body
- 20A 480V AC
- 2-Pole 3-Wire Grounding
- Terminal Screw

Application

High Ampacity Connections

General

Catalog Number	320C7W
Color	Red
EU RoHS Indicator	Yes
Environmental Conditions	Watertight
Insulation	Insulated Body
Item Type	Watertight
Material	Composite
Material - Mounting Hardware	Cord Mounted
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Series	Watertight - IP67
Temperature Rating	Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact, -25° with impact.

Type	Connector
UPC	781786250314

Dimensions

Display Size	Standard Sized Product
--------------	------------------------

Electrical Ratings

Amperage Rating	20 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	20 A
Current Rating	20 A
Voltage Rating	480 VAC
Voltage Rating Description	480V AC

Conductor Related

Conductor Range	#14 AWG to #10 AWG
Number Of Wires	3-Wire
Number of Conductors	3-Wire Grounding

Certifications And Compliance

Nema Rating	Non-NEMA
-------------	----------

Product Assets

[Specifications - 320C7W](#)