



Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Female Receptacle, 20A 250V AC, 2-Pole 3-Wire Grounding, Terminal Screw, Watertight

By Bryant
Catalog # 320R6W



Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Female Receptacle, 20A 250V AC, 2-Pole 3-Wire Grounding, Terminal Screw, Blue, Watertight

Features

- Industrial Grade
- Female Receptacle
- 20A 250V AC
- 2-Pole 3-Wire Grounding
- Terminal Screw

Application

High Ampacity Connections

General

Catalog Number	320R6W
Color	Blue
EU RoHS Indicator	Yes
Environmental Conditions	Watertight
Item Type	Single Flanged
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Series	Watertight - IP67
Type	Receptacle
UPC	781786250369

Dimensions

Display Size

Standard Sized Product

Electrical Ratings

Amperage Rating	20 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	20 A
Current Rating	20 A
Phase	Single Phase
Voltage Rating	250 VAC
Voltage Rating Description	250V AC
Wattage	5000

Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #10 AWG

Certifications And Compliance

Nema Rating	Non-NEMA
Standards - RoHS Compliance Status	CM

Product Assets

[Specifications - 320R6W](#)