



Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Female Receptacle, 20A 480V AC, 2-Pole 3-Wire Grounding, Terminal Screw, Watertight

By Bryant
Catalog # 320R7W



Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Female Receptacle, 20A 480V AC, 2-Pole 3-Wire Grounding, Terminal Screw, Red, Watertight

Application

High Ampacity Connections

General

Color	Red
Environmental Conditions	Watertight
Item Type	Single Flanged
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Series	Watertight - IP67
Type	Receptacle
UPC	781786250376

Dimensions

Display Size	Standard Sized Product
--------------	------------------------

Electrical Ratings

Amperage Rating	20 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	20 A
Current Rating	20 A
Phase	Single Phase
Voltage Rating	480 VAC
Voltage Rating Description	480V AC
Wattage	5540

Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #10 AWG

Certifications and Compliance

Nema Rating	Non-NEMA
-------------	----------

Product Assets

[Catalog Page - Bryant K-4 Catalog page](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-320R7W-SPEC-EN | REV 5/2023