



Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Female Connector Body, 30A 250V AC, Watertight

By Bryant
Catalog # [330C6W](#)



Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Female Connector Body, 30A 250V AC, 2-Pole 3-Wire Grounding, Terminal Screw, Blue, Watertight

Features

- Industrial Grade
- Female Connector Body
- 30A 250V AC
- 2-Pole 3-Wire Grounding
- Terminal Screw

Application

High Ampacity Connections

General

Catalog Number	330C6W
Color	Blue
EU RoHS Indicator	Yes
Environmental Conditions	Watertight
Insulation	Insulated Body
Item Type	Watertight
Material	Composite
Material - Mounting Hardware	Cord Mounted
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Series	Watertight - IP67
Temperature Rating	Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact, -25° with impact.

Type	Connector
UPC	781786250413

Dimensions

Display Size	Standard Sized Product
--------------	------------------------

Electrical Ratings

Amperage Rating	30 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	30 A
Current Rating	30 A
Voltage Rating	250 VAC
Voltage Rating Description	250V AC

Conductor Related

Conductor Range	#12 AWG to #8 AWG
Number Of Wires	3-Wire
Number of Conductors	3-Wire Grounding

Certifications And Compliance

Nema Rating	Non-NEMA
-------------	----------

Product Assets

[Specifications - 330C6W](#)