



Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Female Receptacle, 30A 125V AC, 2-Pole 3-Wire Grounding, Terminal Screw, Watertight

By Bryant
Catalog # [330R4W](#)



Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Female Receptacle, 30A 125V AC, 2-Pole 3-Wire Grounding, Terminal Screw, Yellow, Watertight

Application

High Ampacity Connections

General

| | |
|------------------------------|-------------------|
| Color | Yellow |
| Environmental Conditions | Watertight |
| Item Type | Single Flanged |
| Material | Composite |
| Material - Mounting Hardware | Screw Mounting |
| Number Of Poles | 2-Pole |
| OEM Brand Name | Hubbell Bryant |
| Series | Watertight - IP67 |
| Type | Receptacle |
| UPC | 781786250468 |

Dimensions

| | |
|--------------|------------------------|
| Display Size | Standard Sized Product |
|--------------|------------------------|

Electrical Ratings

| | |
|----------------------------|--------------------------|
| Amperage Rating | 30 A |
| Connectivity | Pressure Terminal Screws |
| Current / Amperage Rating | 30 A |
| Current Rating | 30 A |
| Phase | Single Phase |
| Voltage Rating | 125 VAC |
| Voltage Rating Description | 125V AC |
| Wattage | 3750 |

Conductor Related

| | |
|-----------------|-------------------|
| Number Of Wires | 3-Wire |
| Wire Size | #12 AWG to #8 AWG |

Certifications and Compliance

| | |
|-------------|----------|
| Nema Rating | Non-NEMA |
|-------------|----------|

Product Assets

[Catalog Page - Bryant K-4 Catalog page](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-330R4W-SPEC-EN | REV 5/2023