



Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Female Receptacle, 30A 250V AC, 2-Pole 3-Wire Grounding, Terminal Screw, Watertight

By Bryant
Catalog # 330R6W

Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Female Receptacle, 30A 250V AC, 2-Pole 3-Wire Grounding, Terminal Screw, Blue, Watertight

Features

- Industrial Grade
- Female Receptacle
- 30A 250V AC
- 2-Pole 3-Wire Grounding
- Terminal Screw

Application

High Ampacity Connections

General

Catalog Number	330R6W
Color	Blue
EU RoHS Indicator	Yes
Environmental Conditions	Watertight
Item Type	Single Flanged
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Series	Watertight - IP67
Type	Receptacle
UPC	781786250475

Dimensions



Display Size

Standard Sized Product

Electrical Ratings

Amperage Rating	30 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	30 A
Current Rating	30 A
Phase	Single Phase
Voltage Rating	250 VAC
Voltage Rating Description	250V AC
Wattage	7500

Conductor Related

Number Of Wires	3-Wire
Wire Size	#12 AWG to #8 AWG

Certifications And Compliance

Nema Rating	Non-NEMA
Standards - RoHS Compliance Status	CM

Product Assets

[Specifications - 330R6W](#)