



Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Female Connector Body, 32A 200-240V, Splash Proof

By Bryant
Catalog # [332C6S](#)



Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Female Connector Body, 32A 200-240V, 2-Pole 3-Wire Grounding, Terminal Screw, Blue, Splash Proof

Application

High Ampacity Connections

General

Color	Red
Environmental Conditions	Watertight
Insulation	Insulated Body
Item Type	Splashproof
Material	Composite
Material - Mounting Hardware	Cord Mounted
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Series	Splashproof - IP44
Temperature Rating	Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact, -25° with impact.
Type	Connector
UPC	781786252219

Dimensions

Display Size Standard Sized Product

Electrical Ratings

Amperage Rating	32 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	32 A
Current Rating	32 A
Voltage Rating	380-415 V
Voltage Rating Description	380-415V

Conductor Related

Conductor Range	#12 AWG to #8 AWG
Number Of Conductors	3-Wire Grounding
Number Of Wires	3-Wire

Certifications and Compliance

Nema Rating	Non-NEMA
-------------	----------

Product Assets

[Catalog Page - Bryant K-7 Catalog page](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-332C6S-SPEC-EN | REV 5/2023