



Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Female Connector Body, 32A 220-240V, Watertight

By Bryant
Catalog # [332C6W](#)



Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Female Connector Body, 32A 220-240V, 2-Pole 3-Wire Grounding, Terminal Screw, Blue, Watertight

Application

High Ampacity Connections

General

| | |
|------------------------------|---|
| Color | Blue |
| Environmental Conditions | Watertight |
| Insulation | Insulated Body |
| Item Type | Watertight |
| Material | Composite |
| Material - Mounting Hardware | Cord Mounted |
| Number Of Poles | 2-Pole |
| OEM Brand Name | Hubbell Bryant |
| Series | Watertight - IP67 |
| Temperature Rating | Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact, -25° with impact. |
| Type | Connector |
| UPC | 781786250529 |

Dimensions

| | |
|--------------|------------------------|
| Display Size | Standard Sized Product |
|--------------|------------------------|

Electrical Ratings

| | |
|----------------------------|--------------------------|
| Amperage Rating | 32 A |
| Connectivity | Pressure Terminal Screws |
| Current / Amperage Rating | 32 A |
| Current Rating | 32 A |
| Voltage Rating | 200-250 V |
| Voltage Rating Description | 200-250V |

Conductor Related

| | |
|----------------------|-------------------|
| Conductor Range | #12 AWG to #8 AWG |
| Number Of Conductors | 3-Wire Grounding |
| Number Of Wires | 3-Wire |

Certifications and Compliance

| | |
|-------------|----------|
| Nema Rating | Non-NEMA |
|-------------|----------|

Product Assets

[Catalog Page - Bryant K-5 Catalog page](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-332C6W-SPEC-EN | REV 5/2023