



## Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Female Receptacle, 32A 220-240V, Splash Proof

By Bryant  
Catalog # [332R6S](#)



Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Female Receptacle, 32A 220-240V, 2-Pole 3-Wire Grounding, Terminal Screw, Blue, Splash Proof

### Application

High Ampacity Connections

### General

Color	Red
Environmental Conditions	Splash Proof
Item Type	Single Flanged
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Series	Splashproof - IP44
Type	Receptacle
UPC	781786252257

### Dimensions

Display Size	Standard Sized Product
--------------	------------------------

### Electrical Ratings

Amperage Rating	32 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	32 A
Current Rating	32 A
Phase	Single Phase
Voltage Rating	380-415 V
Voltage Rating Description	380-415V
Wattage	8000

### Conductor Related

Number Of Wires	3-Wire
Wire Size	#12 AWG to #8 AWG

### Certifications and Compliance

Nema Rating	Non-NEMA
-------------	----------

### Product Assets

[Catalog Page - Bryant K-7 Catalog page](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRY-332R6S-SPEC-EN | REV 5/2023