



# Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Female Receptacle, 32A 220-240V, Watertight

By Bryant  
Catalog # 332R6W



Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Female Receptacle, 32A 220-240V, 2-Pole 3-Wire Grounding, Terminal Screw, Blue, Watertight

## General

Application	High Ampacity Connections
Catalog Number	332R6W
Color	Blue
EU RoHS Indicator	Yes
Environmental Conditions	Watertight
Item Type	Single Flanged
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Series	Watertight - IP67
Type	Receptacle
UPC	781786250567

## Dimensions

Display Size	Standard Sized Product
--------------	------------------------

## Electrical Ratings

Amperage Rating	32 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	32 A
Current Rating	32 A
Phase	Single Phase
Voltage Rating	200-250 V
Voltage Rating Description	200-250V
Wattage	8000

## Conductor Related

Number Of Wires	3-Wire
Wire Size	#12 AWG to #8 AWG

## Certifications And Compliance

Nema Rating	Non-NEMA
-------------	----------

## Product Assets



A Hubbell brand