



Locking Devices, Locking Devices, Industrial, Flush Receptacle, 30A 250V, 2-Pole 3-Wire Grounding, Non-NEMA, Screw Terminal, Black

By Bryant
Catalog # 3330



Locking Devices, Locking Devices, Industrial, Flush Receptacle,
30A 250V, 2-Pole 3-Wire Grounding, Non-NEMA, Screw
Terminal, Black

Features

- Combination back and side wiring terminals accept #14 through #8 AWG solid or stranded conductors
- Heavy duty mounting straps are nickel-plated to resist corrosion, wide width design assures secure assembly
- NEMA rating and configuration are molded into face for easy identification
- One-piece, rivetless copper-alloy contact design reduces heat buildup and provides secure blade retention

Application

Extra Heavy Duty Industrial Specification Grade

General

Catalog Number	3330
EU RoHS Indicator	No
Environmental Conditions	Indoor Only
Item Type	30A Single Nylon Receptacle
Material	Nylon
Material - Mounting Hardware	Plug-In
Number Of Poles	3-Pole
OEM Brand Name	Hubbell Bryant
Style	Single Receptacle
Type	Receptacle
UPC	781786619685

Dimensions

Dimensions 3.28 in x 1.71 in x 1.20 in

Display Size	Standard Sized Product
Height	1.2 in
Length	3.28 in
Width	1.71 in

Electrical Ratings

Amperage Rating	30 A
Connectivity	Terminal Screws
Current Rating	30 A
Phase	Multi Phase
Voltage Rating	125/250 VAC
Voltage Rating Description	125/250V AC

Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #8 AWG

Certifications And Compliance

Nema Rating	Non-NEMA
-------------	----------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - BRY Q-18 Catalog Page](#)
[Catalog Page - BRY H-17 Catalog Page](#)
[Catalogs - Bryant Full Line Catalog](#)
[Specifications - 3330](#)