



# Locking Devices, Locking Devices, Industrial, Flush Receptacle, 30A 3-Phase Delta 250V AC, 3-Pole 4-Wire Grounding, Non-NEMA, Screw Terminal, Black

By Bryant  
Catalog # 3430G



Locking Devices, Industrial, Flush Receptacle, 30A 250V AC, 3-Pole 4-Wire Grounding, Non-NEMA, Screw Terminal, Black.

## Features

- Flush Receptacle
- 30A 250V AC
- 3-Pole 4-Wire Grounding
- Non-NEMA
- Screw Terminal

## Application

Extra Heavy Duty Industrial Specification Grade

## General

Catalog Number	3430G
EU RoHS Indicator	No
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	30A Single Nylon Receptacle-For Replacement Use
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	3-Pole
OEM Brand Name	Hubbell Bryant
Style	Single Receptacle
Type	Receptacle
UPC	781786619913

## Dimensions

Dimensions 3.28 in x 1.70 in x 1.24 in

Display Size	Standard Sized Product
Height	1.24 in
Length	3.28 in
Width	1.7 in

## Electrical Ratings

Amperage Rating	30 A
Connectivity	Terminal Screws
Current Rating	30 A
Phase	Single Phase
Voltage Rating	3 Phase 250 VAC
Voltage Rating Description	3 Phase 250V AC

## Conductor Related

Number Of Wires	4-Wire
Wire Size	#14 AWG to #8 AWG

## Certifications And Compliance

Nema Rating	Non-NEMA
-------------	----------

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

[Catalog Page - BRY H-17 Catalog Page](#)  
[Catalogs - Bryant Full Line Catalog](#)  
[Specifications - 3430G](#)