



Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Female Connector Body, 60A 250V AC, Watertight

By Bryant
Catalog # [360C6W](#)



Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Female Connector Body, 60A 250V AC, 2-Pole 3-Wire Grounding, Terminal Screw, Blue, Watertight

Application

High Ampacity Connections

General

Color	Blue
Environmental Conditions	Watertight
Insulation	Insulated Body
Item Type	Watertight
Material	Composite
Material - Mounting Hardware	Cord Mounted
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Series	Watertight - IP67
Temperature Rating	Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact, -25° with impact.
Type	Connector
UPC	781786250611

Dimensions

Display Size	Standard Sized Product
--------------	------------------------

Electrical Ratings

Amperage Rating	60 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	60 A
Current Rating	60 A
Voltage Rating	250 VAC
Voltage Rating Description	250V AC

Conductor Related

Conductor Range	#8 AWG to #2 AWG
Number Of Conductors	3-Wire Grounding
Number Of Wires	3-Wire

Certifications and Compliance

Nema Rating	Non-NEMA
-------------	----------

Product Assets

[Catalog Page - Bryant K-4 Catalog page](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-360C6W-SPEC-EN | REV 5/2023