



# Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Female Receptacle, 60A 125V AC, 2-Pole 3-Wire Grounding, Terminal Screw, Watertight

By Bryant  
Catalog # 360R4W

Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Female Receptacle, 60A 125V AC, 2-Pole 3-Wire Grounding, Terminal Screw, Yellow, Watertight

## Features

- Industrial Grade
- Female Receptacle
- 60A 125V AC
- 2-Pole 3-Wire Grounding
- Terminal Screw

## Application

High Ampacity Connections

## General

Catalog Number	360R4W
Color	Yellow
EU RoHS Indicator	Yes
Environmental Conditions	Watertight
Item Type	Single Flanged
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Series	Watertight - IP67
Type	Receptacle
UPC	781786250666



## Dimensions

Display Size Standard Sized Product

## Electrical Ratings

Amperage Rating	60 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	60 A
Current Rating	60 A
Phase	Single Phase
Voltage Rating	125 VAC
Voltage Rating Description	125V AC
Wattage	7500

## Conductor Related

Number Of Wires	3-Wire
Wire Size	#8 AWG to #2 AWG

## Certifications And Compliance

Nema Rating	Non-NEMA
-------------	----------

## Product Assets

[Specifications - 360R4W](#)