



# Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Female Receptacle, 60A 250V AC, 2-Pole 3-Wire Grounding, Terminal Screw, Watertight

By Bryant  
Catalog # 360R6W



Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Female Receptacle, 60A 250V AC, 2-Pole 3-Wire Grounding, Terminal Screw, Blue, Watertight

### Application

High Ampacity Connections

### General

Color	Blue
EU RoHS Indicator	Yes
Environmental Conditions	Watertight
Item Type	Single Flanged
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Series	Watertight - IP67
Type	Receptacle
UPC	781786250673

### Dimensions

Display Size	Standard Sized Product
--------------	------------------------

### Electrical Ratings

Amperage Rating	60 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	60 A
Current Rating	60 A
Phase	Single Phase
Voltage Rating	250 VAC
Voltage Rating Description	250V AC
Wattage	15000

### Conductor Related

Number Of Wires	3-Wire
Wire Size	#8 AWG to #2 AWG

### Certifications And Compliance

Nema Rating	Non-NEMA
-------------	----------

### Product Assets



A proud member of the Hubbell Family.