



Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Female Receptacle, 63A 220-240V, Watertight

By Bryant
Catalog # 363R6W



Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Female Receptacle, 63A 220-240V, 2-Pole 3-Wire Grounding, Terminal Screw, Blue, Watertight

Features

- Industrial Grade
- Female Receptacle
- 63A 220-240V
- 2-Pole 3-Wire Grounding
- Terminal Screw

Application

High Ampacity Connections

General

Catalog Number	363R6W
Color	Blue
EU RoHS Indicator	Yes
Environmental Conditions	Watertight
Item Type	Single Flanged
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Series	Watertight - IP67
Type	Receptacle
UPC	781786250727

Dimensions

Display Size Standard Sized Product

Electrical Ratings

Amperage Rating	63 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	63 A
Current Rating	63 A
Phase	Single Phase
Voltage Rating	200-250 V
Voltage Rating Description	200-250V
Wattage	15750

Conductor Related

Number Of Wires	3-Wire
Wire Size	#8 AWG to #2 AWG

Certifications And Compliance

Nema Rating	Non-NEMA
-------------	----------

Product Assets

[Specifications - 363R6W](#)