



# Locking Devices, Locking Devices, Industrial, Male Plug, 50A 250V DC 600V AC, 2-Pole 3-Wire Grounding, Non-NEMA, Screw Terminal, Black and White

By Bryant  
Catalog # 3763



Locking Devices, Industrial, Male Plug, 50A 250V DC/600V AC, 2-Pole 3-Wire Grounding, Non-NEMA, Screw Terminal, Heavy duty Black

## Application

Extra Heavy Duty Industrial

## General

Color	Black
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	50A Male Plug-For Replacement Use
Material	Composite
Material - Mounting Hardware	Cord Mounted
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Style	Extra Heavy Duty
Type	Plugs
UPC	781786652507

## Dimensions

Dimensions	5.38 in x 2.56 in x 2.56 in
Display Size	Standard Sized
Height	2.56 in
Length	5.38 in
Width	2.56 in

## Electrical Ratings

Amperage Rating	50 A
Connectivity	Screw Terminals
Current Rating	50 A
Phase	Multi Phase
Voltage Rating	250 VDC/600 VAC
Voltage Rating Description	250 VDC/600 VAC

## Conductor Related

Cord Type	All Listed Portables
Number Of Wires	3-Wire
Wire Size	#18 AWG to #8 AWG

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

[Catalog Page - Bryant H-22 Catalog page](#)  
[Catalogs - Bryant Full Line Catalog](#)

## Related Products

[3762 - Locking Devices, Locking Devices, Industrial, Female Connector Body, 50A 250V DC/600V AC, 2-Pole 3-Wire Grounding, Non-NEMA, Screw Terminal and White](#)  
[3771 - Locking Devices, Locking Devices, Industrial, Flush Receptacle, 50A 250V DC/600V AC, 2-Pole 3-Wire Grounding, Non-NEMA, Screw Terminal, Black](#)  
[7716B - Locking Devices, Accessories, Weatherproof Boot, Nylon Plug, For 50A Black](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRY-3763-SPEC-EN | REV 5/2023