



## Straight Blade Devices, Specialty Receptacles, Floor Mounted, Receptacle and Plate, 15A 125V, 5-15R, Smooth Brushed Brass Finish

By Bryant  
Catalog # [3799G](#)

Straight Blade Devices, Specialty Receptacles, Floor Mounted, Receptacle and Plate, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, Smooth Brushed Brass Finish, Single Pack



### Application

Commercial/Industrial

### General

Color	Brass
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Display Case Receptacle Single
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Series	Special Use
Style	Display Receptacles
Type	Single Receptacle
UPC	781786620254

### Dimensions

Dimensions	4.50 in x 2.75 in x 1.86 in
Display Size	Standard Sized Product
Height	1.86 in
Length	4.50 in
Weight	0.5 lb
Width	2.75 in

### Electrical Ratings

Amperage Rating	15 A
Current / Amperage Rating	15 A
Current Rating	15 A
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V
Wattage	1875

### Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #12 AWG

### Certifications and Compliance

Nema Rating	5-15R
-------------	-------

### Logistics

Carton Quantity	10
-----------------	----

### Product Assets

[Catalog Page - Bryant A-24 Catalog page](#)  
[Catalogs - Bryant Full Line Catalog](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRY-3799G-SPEC-EN | REV 5/2023