



# Straight Blade Devices, Specialty Receptacles, Floor Mounted, Receptacle and Plate, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, Nickel Plated Finish

By Bryant  
Catalog # 3799GS



Straight Blade Devices, Specialty Receptacles, Floor Mounted, Receptacle and Plate, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, Nickel Plated Finish, Single Pack

## General

Application	Commercial/Industrial
Catalog Number	3799GS
Color	Nickel
EU RoHS Indicator	No
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Display Case Receptacle Single
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Series	Special Use
Style	Display Receptacles
Type	Single Receptacle
UPC	781786730748

## Dimensions

Dimensions	4.50 in x 2.75 in x 1.86 in
Display Size	Standard Sized Product
Height	1.86 in
Length	4.5 in
Weight	0.3 lb
Width	2.75 in

## Electrical Ratings

Amperage Rating	15 A
Current / Amperage Rating	15 A
Current Rating	15 A
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V
Wattage	1875

## Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #12 AWG

## Certifications And Compliance

Nema Rating	5-15R
-------------	-------

## Logistics

Carton Quantity	10
Pallet Quantity	2340

## Product Assets

[Catalog Page - BRY A-24 Catalog Page](#)  
[Catalogs - Bryant Full Line Catalog](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
BRY-3799GS-SPEC-EN | REV 6/2024