



Switches and Lighting Controls, Industrial Grade, Toggle Switches, Motor Disconnects, Three Pole, 40A, 600V AC, Side Wired Only, Black

By Bryant
Catalog # 40003D



Switches and Lighting Controls, Industrial Grade, Toggle
Switches, Motor Disconnects, Three Pole, 40A, 600V AC, Side
Wired Only, Black

General

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Open Switch
Load Capacity	Inductive
Material - Mounting Hardware	Screw Mounting
Number Of Poles	3 Pole
OEM Brand Name	Hubbell Bryant
Operating Cycles	10,000 Cycles Minimum
Operating Temperature	Minimum Continuous -40 Deg C without Impact
Series	Standard Toggle
Style	Motor Controller/Disconnect
Type	Side Wire
UPC	781786631656

Dimensions

Display Size	Standard Sized Product
--------------	------------------------

Electrical Ratings

Amperage Rating	40 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	40 A
Current Rating	40 A
Phase	Three Phase
Voltage Rating	600V AC kV
Voltage Rating Description	600V AC kV
Wattage	24000

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - Bryant E-12 Catalog page](#)
[Catalog Page - Bryant G-6 Catalog page](#)
[Catalog Page - Bryant G-2 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)
[Literature - General Literature - Motor Controllers and
Disconnects](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-40003D-SPEC-EN | REV 5/2023