



Switches and Lighting Controls, Industrial Grade, Toggle Switches, Manual Motor Controllers, Double Pole, 40A 120/277V AC, Side Wired Only, Brown

By Bryant
Catalog # [4002](#)



Switches and Lighting Controls, Industrial Grade, Toggle
Switches, Manual Motor Controllers, Double Pole, 40A
120/277V AC, Side Wired Only, Brown

General

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Open Switch
Load Capacity	Inductive
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2 Pole
OEM Brand Name	Hubbell Bryant
Operating Cycles	10,000 Cycles Minimum
Operating Temperature	Minimum Continuous -40 Deg C without Impact
Series	Standard Toggle
Style	Motor Controller Only
Type	Side Wire
UPC	781786925335

Dimensions

Display Size	Standard Sized Product
--------------	------------------------

Electrical Ratings

Amperage Rating	30 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	30 A
Current Rating	40 A
Phase	Single Phase
Voltage Rating	600V AC kV
Voltage Rating Description	600V AC kV
Wattage	24000

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - BRY G-2 Catalog Page](#)
[Catalogs - Bryant Full Line Catalog](#)



A proud member of the Hubbell Family.