



Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Female Receptacle 100A 125/250V, Screw Terminals, Watertight

By Bryant
Catalog # 4100R12W



Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Female Receptacle 100A 125/250V, 3-Pole 4-Wire Grounding, Screw Terminals, Orange, Watertight

Features

- Industrial Grade
- Female Receptacle 100A 125/250V
- 3-Pole 4-Wire Grounding
- Screw Terminals
- Orange

Application

High Ampacity Connections

General

Catalog Number	4100R12W
Color	Orange
EU RoHS Indicator	Yes
Environmental Conditions	Watertight
Item Type	Single Flanged
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	3-Pole
OEM Brand Name	Hubbell Bryant
Series	Watertight - IP67
Type	Receptacle
UPC	781786250857

Dimensions

Display Size Standard Sized Product

Electrical Ratings

Amperage Rating	100 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	100 A
Current Rating	100 A
Phase	Single Phase
Voltage Rating	<ul style="list-style-type: none">• 125 VAC• 250 VAC
Voltage Rating Description	125/250V AC
Wattage	25000

Conductor Related

Number Of Wires	4-Wire
Wire Size	#3 AWG to #1/0 AWG

Certifications And Compliance

Nema Rating	Non-NEMA
-------------	----------

Product Assets

[Specifications - 4100R12W](#)