



# Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Female Receptacle, 100A 3-Phase Delta 250V AC, 3-Pole 4-WireGrounding, Watertight

By Bryant  
Catalog # [4100R9W](#)



Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Female Receptacle, 100A 3-Phase Delta 250V AC, 3-Pole 4-WireGrounding, Screw Terminals, Blue, Watertight

## Application

High Ampacity Connections

## General

Color	Blue
Environmental Conditions	Watertight
Item Type	Single Flanged
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	3-Pole
OEM Brand Name	Hubbell Bryant
Series	Watertight - IP67
Type	Receptacle
UPC	781786250888

## Dimensions

Display Size	Standard Sized Product
--------------	------------------------

## Electrical Ratings

Amperage Rating	100 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	100 A
Current Rating	100 A
Phase	Three Phase
Voltage Rating	3 Phase 250 V
Voltage Rating Description	3 Phase 250V
Wattage	25000

## Conductor Related

Number Of Wires	4-Wire
Wire Size	#3 AWG to #1/0 AWG

## Certifications and Compliance

Nema Rating	Non-NEMA
-------------	----------

## Product Assets

[Catalog Page - Bryant K-5 Catalog page](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRY-4100R9W-SPEC-EN | REV 5/2023