



Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Male Flanged Inlet, 20A 25/250V, Screw Terminals, Watertight

By Bryant
Catalog # 420B12W



Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Male Flanged Inlet, 20A 25/250V, 3-Pole 4-Wire Grounding, Screw Terminals, Red, Watertight

Features

- Industrial Grade
- Male Flanged Inlet
- 20A 25/250V
- 3-Pole 4-Wire Grounding
- Screw Terminals

Application

High Ampacity Watertight Connections

General

Catalog Number	420B12W
Color	Orange
EU RoHS Indicator	Yes
Environmental Conditions	Watertight
Insulation	Insulated Body
Item Type	Single Flanged
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	3-Pole
OEM Brand Name	Hubbell Bryant
Series	Watertight - IP67
Temperature Rating	Maximum Continuous: 75° C; Minimum Continuous: -40° C

Type	w/o impact
UPC	Inlet 781786250970

Dimensions

Display Size	Standard Sized Product
--------------	------------------------

Electrical Ratings

Amperage Rating	20 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	20 A
Current Rating	20 A
Dielectric Strength	Withstands 3000V Minimum in
Voltage Rating	<ul style="list-style-type: none">• 125 VAC• 250 VAC
Voltage Rating Description	125/250V AC
Wattage	5000

Conductor Related

Number Of Wires	4-Wire
-----------------	--------

Product Assets

[Specifications - 420B12W](#)