



Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Female Connector Body, 20A 3-Phase Delta 480V AC, Watertight

By Bryant
Catalog # [420C7W](#)



Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Female Connector Body, 20A 3-Phase Delta 480V AC, 3-Pole 4-Wire Grounding, Screw Terminals, Red, Watertight

Features

- Industrial Grade
- Female Connector Body
- 20A 3-Phase Delta 480V AC
- 3- Pole 4-Wire Grounding
- Screw Terminals

Application

High Ampacity Connections

General

Catalog Number	420C7W
Color	Red
EU RoHS Indicator	Yes
Environmental Conditions	Watertight
Insulation	Insulated Body
Item Type	Watertight
Material	Composite
Material - Mounting Hardware	Cord Mounted
Number Of Poles	3-Pole
OEM Brand Name	Hubbell Bryant
Series	Watertight - IP67
Temperature Rating	Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact, -25° with impact.

Type	Connector
UPC	781786251038

Dimensions

Display Size	Standard Sized Product
--------------	------------------------

Electrical Ratings

Amperage Rating	20 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	20 A
Current Rating	20 A
Voltage Rating	3 Phase 480 V
Voltage Rating Description	3 Phase 480V

Conductor Related

Conductor Range	#14 AWG to #10 AWG
Number Of Wires	4-Wire
Number of Conductors	4-Wire Grounding

Certifications And Compliance

Nema Rating	Non-NEMA
-------------	----------

Product Assets

[Specifications - 420C7W](#)