



Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Female Receptacle, 20A 3-Phase Delta 600V AC, Screw Terminals, Watertight

By Bryant
Catalog # 420R5W



Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Female Receptacle, 20A 3-Phase Delta 600V AC, 3-Pole 4-Wire Grounding, Screw Terminals, Black, Watertight

General

Application	High Ampacity Connections
Catalog Number	420R5W
Color	Black
EU RoHS Indicator	Yes
Environmental Conditions	Watertight
Item Type	Single Flanged
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	3-Pole
OEM Brand Name	Hubbell Bryant
Series	Watertight - IP67
Type	Receptacle
UPC	781786251106

Dimensions

Display Size	Standard Sized Product
--------------	------------------------

Electrical Ratings

Amperage Rating	20 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	20 A
Current Rating	20 A
Phase	Three Phase
Voltage Rating	3 Phase 600 V
Voltage Rating Description	3 Phase 600V
Wattage	12000

Conductor Related

Number Of Wires	4-Wire
Wire Size	#14 AWG to #10 AWG

Certifications And Compliance

Nema Rating	Non-NEMA
-------------	----------

Product Assets



A Hubbell brand