



Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Female Receptacle, 20A 3-Phase Delta 250V AC, Screw Terminals, Watertight

By Bryant
Catalog # 420R9W



Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Female Receptacle, 20A 3-Phase Delta 250V AC, 3-Pole 4-Wire Grounding, Screw Terminals, Blue, Watertight

Application

High Ampacity Connections

General

Color	Blue
Environmental Conditions	Watertight
Item Type	Single Flanged
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	3-Pole
OEM Brand Name	Hubbell Bryant
Series	Watertight - IP67
Type	Receptacle
UPC	781786251120

Dimensions

Display Size	Standard Sized Product
--------------	------------------------

Electrical Ratings

Amperage Rating	20 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	20 A
Current Rating	20 A
Phase	Three Phase
Voltage Rating	3 Phase 250 V
Voltage Rating Description	3 Phase 250V
Wattage	5000

Conductor Related

Number Of Wires	4-Wire
Wire Size	#14 AWG to #10 AWG

Certifications and Compliance

Nema Rating	Non-NEMA
-------------	----------

Product Assets

[Catalog Page - Bryant K-4 Catalog page](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-420R9W-SPEC-EN | REV 5/2023