



Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Male Flanged Inlet, 30A 125/250V, Screw Terminals, Watertight

By Bryant
Catalog # 430B12W



Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Male Flanged Inlet, 30A 125/250V, 3-Pole 4-Wire Grounding, Screw Terminals, Orange, Watertight

General

Application	High Ampacity Watertight Connections
Catalog Number	430B12W
Color	Orange
EU RoHS Indicator	Yes
Environmental Conditions	Watertight
Insulation	Insulated Body
Item Type	Single Flanged
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	3-Pole
OEM Brand Name	Hubbell Bryant
Series	Watertight - IP67
Temperature Rating	Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact
Type	Inlet
UPC	781786251137

Dimensions

Display Size	Standard Sized Product
--------------	------------------------

Electrical Ratings

Amperage Rating	30 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	30 A
Current Rating	30 A
Dielectric Strength	Withstands 3000V Minimum in
Voltage Rating	125 VAC 250 VAC
Voltage Rating Description	125/250V AC
Wattage	7500

Conductor Related

Number Of Wires	4-Wire
-----------------	--------

Product Assets



A Hubbell brand