



# Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Male Plug, 30A 125/250V, 3-Pole 4-Wire Grounding, Screw Terminals, Watertight

By Bryant  
Catalog # 430P12W



Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Male Plug, 30A 125/250V, 3-Pole 4-Wire Grounding, Screw Terminals, Orange, Watertight

## Features

- Industrial Grade
- Male Plug
- 30A 125/250V
- 3-Pole 4-Wire Grounding
- Screw Terminals

## Application

High Ampacity Connections

## General

Catalog Number	430P12W
Color	Orange
EU RoHS Indicator	Yes
Environmental Conditions	Watertight
Item Type	Male Plug
Material	Composite
Material - Mounting Hardware	Cord Mounted
Number Of Poles	3-Pole
OEM Brand Name	Hubbell Bryant
Series	Watertight - IP67
Type	Plugs
UPC	781786251212

## Dimensions

Display Size

Standard Sized

## Electrical Ratings

Amperage Rating	30 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	30 A
Current Rating	30 A
Phase	Single Phase
Voltage Rating	<ul style="list-style-type: none"> <li>• 125 VAC</li> <li>• 250 VAC</li> </ul>
Voltage Rating Description	125 VAC;250 VAC
Wattage	7500

## Conductor Related

Cord Type	All Portable
Number Of Wires	4-Wire
Wire Size	#12 AWG to #8 AWG

## Certifications And Compliance

Nema Rating	Non-NEMA
-------------	----------

## Product Assets

[Specifications - 430P12W](#)

