

## Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Female Connector Body, 32A 380-480V, Screw Terminals, Watertight

By Bryant  
Catalog # [432C3W](#)



Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Female Connector Body, 32A 380-480V, 3-Pole 4-Wire Grounding, Screw Terminals, Red, Watertight

### Features

- Industrial Grade
- Female Connector Body
- 32A 380-480V
- 3-Pole 4-Wire Grounding
- Screw Terminals

### Application

High Ampacity Connections

### General

Catalog Number	432C3W
EU RoHS Indicator	Yes
Environmental Conditions	Watertight
Insulation	Insulated Body
Item Type	Watertight
Material	Composite
Material - Mounting Hardware	Cord Mounted
Number Of Poles	3-Pole
OEM Brand Name	Hubbell Bryant
Series	Watertight - IP67
Temperature Rating	Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact, -25° with impact.

Type	Connector
UPC	781786251304

### Dimensions

Display Size	Standard Sized Product
--------------	------------------------

### Electrical Ratings

Amperage Rating	32 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	32 A
Current Rating	32 A
Voltage Rating	50Hz 380 V / 60Hz 440 V
Voltage Rating Description	380V 50Hz 440V 60Hz

### Conductor Related

Conductor Range	#12 AWG to #8 AWG
Number Of Wires	4-Wire
Number of Conductors	4-Wire Grounding

### Certifications And Compliance

Nema Rating	Non-NEMA
-------------	----------

### Product Assets

[Specifications - 432C3W](#)