



# Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Female Receptacle, 32A 380-480V, Screw Terminals, Watertight

By Bryant  
Catalog # [432R3W](#)



Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Female Receptacle, 32A 380-480V, 3-Pole 4-Wire Grounding, Screw Terminals, Red, Watertight

## Features

- Industrial Grade
- Female Receptacle
- 32A 380-480V
- 3-Pole 4-Wire Grounding
- Screw Terminals

## Application

High Ampacity Connections

## General

Catalog Number	432R3W
EU RoHS Indicator	Yes
Environmental Conditions	Watertight
Item Type	Single Flanged
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	3-Pole
OEM Brand Name	Hubbell Bryant
Series	Watertight - IP67
Type	Receptacle
UPC	781786251342

## Dimensions

Display Size Standard Sized Product

## Electrical Ratings

Amperage Rating	32 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	32 A
Current Rating	32 A
Phase	Three Phase
Voltage Rating	50Hz 380 V / 60Hz 440 V
Voltage Rating Description	380V 50Hz 440V 60Hz
Wattage	14080

## Conductor Related

Number Of Wires	4-Wire
Wire Size	#12 AWG to #8 AWG

## Certifications And Compliance

Nema Rating	Non-NEMA
-------------	----------

## Product Assets

[Specifications - 432R3W](#)