



Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Male Flanged Inlet, 60A 3-Phase Delta 250V AC, Screw Terminals, Watertight

By Bryant
Catalog # 460B9W



Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Male Flanged Inlet, 60A 3-Phase Delta 250V AC, 3-Pole 4-Wire Grounding, Screw Terminals, Blue, Watertight

Features

- Industrial Grade
- Male Flanged Inlet
- 60A 3-Phase Delta 250V AC
- 3-Pole 4-Wire Grounding
- Screw Terminals

Application

High Ampacity Watertight Connections

General

Catalog Number	460B9W
Color	Blue
EU RoHS Indicator	Yes
Environmental Conditions	Watertight
Insulation	Insulated Body
Item Type	Single Flanged
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	3-Pole
OEM Brand Name	Hubbell Bryant
Series	Watertight - IP67
Temperature Rating	Maximum Continuous: 75° C; Minimum Continuous: -40° C

Type	w/o impact
UPC	Inlet 781786251397

Dimensions

Display Size	Standard Sized Product
--------------	------------------------

Electrical Ratings

Amperage Rating	60 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	60 A
Current Rating	60 A
Dielectric Strength	Withstands 3000V Minimum in
Voltage Rating	3 Phase 250 V
Voltage Rating Description	3 Phase 250V
Wattage	15000

Conductor Related

Number Of Wires	4-Wire
-----------------	--------

Product Assets

[Specifications - 460B9W](#)