



## Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Female Connector Body, 60A 3-Phase Delta 600V AC, Watertight

By Bryant  
Catalog # [460C5W](#)



Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Female Connector Body, 60A 3-Phase Delta 600V AC, 3- Pole 4-Wire Grounding, Screw Terminals, Black, Watertight

### Application

High Ampacity Connections

### General

Color	Black
Environmental Conditions	Watertight
Insulation	Insulated Body
Item Type	Watertight
Material	Composite
Material - Mounting Hardware	Cord Mounted
Number Of Poles	3-Pole
OEM Brand Name	Hubbell Bryant
Series	Watertight - IP67
Temperature Rating	Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact, -25° with impact.
Type	Connector
UPC	781786251410

### Dimensions

Display Size	Standard Sized Product
--------------	------------------------

### Electrical Ratings

Amperage Rating	60 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	60 A
Current Rating	60 A
Voltage Rating	3 Phase 600 V
Voltage Rating Description	3 Phase 600V

### Conductor Related

Conductor Range	#8 AWG to #2 AWG
Number Of Conductors	4-Wire Grounding
Number Of Wires	4-Wire

### Certifications and Compliance

Nema Rating	Non-NEMA
-------------	----------

### Product Assets

[Catalog Page - Bryant K-4 Catalog page](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRY-460C5W-SPEC-EN | REV 5/2023